



# U-Bent Rapid Start T8

FB32T8/6 TL735 ALTO

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

## Product data

### • General Characteristics

Base	Medium Bi-Pin [Medium Bi-Pin Fluorescent]
Base Information	Green Base
Bulb	T8-6U [U-bent T 8/8 inch with 6" spacing]
Rated Avg. Life [3 hr Start]	20000 hr
Rated Avg Life [12 Hr Start]	24000 hr
Energy Saving	Energy Saving

### • Light Technical Characteristics

Color Code	TL735 [CCT of 3500K]
Color Rendering Index	75 Ra8
Color Designation	TL735
Color Temperature	3500 K
Initial lumen	2650 Lm
Design Mean Lumens	2370 Lm

### • Electrical Characteristics

Watts	32 W
-------	------

### • Environmental Characteristics

Mercury (Hg) Content	3.0 mg
Picogram per Lumen Hour	63 p/LuHr

### • Product Dimensions

Nominal Length [inch]	22.44
-----------------------	-------

### • Product Data

Product number	378935
Full product name	FB32T8/6 TL735 ALTO
Short product name	FB32T8/6 TL735 ALTO
Pieces per Sku	1
eop_pck_cfg	20
Skus/Case	20
Bar code on pack	46677378936
Bar code on case	50046677378931
Logistics code(s)	927860073507
eop_net_weight_pp	0.001 kg

# PHILIPS


sense and simplicity

# U-Bent Rapid Start T8


## Dimensional drawing



G13, T8-U



G13



G13, T8-U



© 2012 Koninklijke Philips Electronics N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2012, August 4  
data subject to change