



PLUS T8 High Output

F96T8 86W/850 R17d HO ALTO Plus 1LP

Philips PLUS T8 High Output 8-foot fluorescent lamps reduce the impact on the environment by offering long life and low mercury.

Product data

• General Characteristics

Base	R17d [Recessed Double Contact Bay (RDC Bay-Fluorescent)]
Base Information	Green Base
Bulb	T8
Rated Avg. Life [3 hr Start]	24000 hr
Rated Avg Life [12 Hr Start]	30000 hr
Energy Saving	Energy Saving

• Light Technical Characteristics

Color Code	TL850 [CCT of 5000K]
Color Rendering Index	85 Ra8
Color Designation	TL850
Color Temperature	5000 K
Initial lumen	8100 Lm
Design Mean Lumens	7525 Lm

• Electrical Characteristics

Watts	86 W
-------	------

• Environmental Characteristics

Mercury (Hg) Content	4.4 mg
Picogram per Lumen Hour	24 p/LuHr

• Product Dimensions

Nominal Length [inch]	96
-----------------------	----


• Product Data

Product number	236893
Full product name	F96T8 86W/850 R17d HO ALTO Plus 1LP
Short product name	F96T8 86W/850 R17d HO ALTO Plus 1LP
Pieces per Sku	1
eop_pck_cfg	25
Skus/Case	25
Bar code on pack	46677236892
Bar code on case	50046677236897
Logistics code(s)	927874085005
eop_net_weight_pp	0.001 kg


PHILIPS

sense and simplicity

Dimensional drawing



R17d, T8



R17d, T8



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change