



PLUS T8 Slimline

F96T8 59W/735 Single Pin ALTO Plus 1LP

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data

• General Characteristics

Base	Single Pin [Single Pin Fluorescent]
Base Information	Green Base
Bulb	T8
Rated Avg. Life [3 hr Start]	24000 hr
Rated Avg Life [12 Hr Start]	30000 hr
Energy Saving	Energy Saving

• Light Technical Characteristics

Color Code	TL735 [CCT of 3500K]
Color Rendering Index	78 Ra8
Color Designation	TL735
Color Temperature	3500 K
Initial lumen	5700 Lm
Design Mean Lumens	5190 Lm

• Electrical Characteristics

Watts	59 W
-------	------

• Environmental Characteristics

Mercury (Hg) Content	4.4 mg
----------------------	--------

Picogram per Lumen Hour	35 p/LuHr
-------------------------	-----------

• Product Dimensions

Nominal Length [inch]	96
-----------------------	----


• Footnotes

Footnotes Fluorescent/CFL	903 [This Bulb Meets US Federal Minimum Efficiency Standard.]
---------------------------	---


• Product Data

Product number	236810
Full product name	F96T8 59W/735 Single Pin ALTO Plus 1LP
Short product name	F96T8 59W/735 Single Pin ALTO Plus 1LP
Pieces per Sku	1
eop_pck_cfg	25
Skus/Case	25
Bar code on pack	46677236816
Bar code on case	50046677236811
Logistics code(s)	927874573505
eop_net_weight_pp	0.001 kg

Dimensional drawing



FA8, T8



FA8, T8



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change