



PLUS T8 Slimline

F96T8 59W/850 Single Pin ALTO Plus 1LP

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data

• General Characteristics

Base	Single Pin [Single Pin Fluorescent]
Base Information	Green Base
Bulb	T8
Rated Avg. Life [3 hr Start]	24000 hr
Rated Avg Life [12 Hr Start]	30000 hr
Energy Saving	Energy Saving

• Light Technical Characteristics

Color Code	TL850 [CCT of 5000K]
Color Rendering Index	85 Ra8
Color Designation	TL850
Color Temperature	5000 K
Initial lumen	5780 Lm
Design Mean Lumens	5375 Lm

• Electrical Characteristics

Watts	59 W
-------	------

• Environmental Characteristics

Mercury (Hg) Content	4.4 mg
----------------------	--------

Picogram per Lumen Hour	34 p/LuHr
-------------------------	-----------

• Product Dimensions

Nominal Length [inch]	96
-----------------------	----

• Footnotes

Footnotes Fluorescent/CFL	903 [This Bulb Meets US Federal Minimum Efficiency Standard.]
---------------------------	---


• Product Data

Product number	236869
Full product name	F96T8 59W/850 Single Pin ALTO Plus 1LP
Short product name	F96T8 59W/850 Single Pin ALTO Plus 1LP
Pieces per Sku	1
eop_pck_cfg	25
Skus/Case	25
Bar code on pack	46677236861
Bar code on case	50046677236866
Logistics code(s)	927874585008
eop_net_weight_pp	0.001 kg


PHILIPS

sense and simplicity

Dimensional drawing



FA8, T8



FA8, T8



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change