



# Retail Sales T8

## F15T8 CW Plus ALTO 1SL

Energy Savings, extra long life, extra low mercury T8 lamps offer high energy savings, superior lumen output, and long life in an environmentally responsible lamp.

### Product data

#### • General Characteristics

Base	Medium Bi-Pin [Medium Bi-Pin Fluorescent]
Base Information	Green Base
Bulb	T8
Rated Avg. Life [3 hr Start]	7500 hr
Life with 3h/day use [years]	3 an

#### • Light Technical Characteristics

Color Code	33
Color Rendering Index	62 Ra8
Color Temperature	4100 K
Initial lumen	1175 Lm
Design Mean Lumens	1035 Lm

#### • Electrical Characteristics

Watts	15 W
-------	------

#### • Environmental Characteristics

Mercury (Hg) Content	1.9 mg
Picogram per Lumen Hour	245 p/LuHr

#### • Product Dimensions

Nominal Length [inch]	24
-----------------------	----

#### • Product Data

Product number	391086
Full product name	F15T8 CW Plus ALTO 1SL
Short product name	F15T8 CW Plus ALTO 1SL
Pieces per Sku	1
eop_pck_cfg	6
Skus/Case	6
Bar code on pack	46677391089
Bar code on case	50046677391084
Logistics code(s)	927875103306
eop_net_weight_pp	0.001 kg


# PHILIPS

sense and simplicity

Dimensional drawing



G13, T8



G13



G13, T8



© 2012 Koninklijke Philips Electronics N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2012, August 4  
data subject to change