



Retail Sales T8

F15T8 CW Plus ALTO

Energy Savings, extra long life, extra low mercury T8 lamps offer high energy savings, superior lumen output, and long life in an environmentally responsible lamp.

Product data

• General Characteristics

Base	Medium Bi-Pin [Medium Bi-Pin Fluorescent]
Base Information	Green Base
Bulb	T8
Rated Avg. Life [3 hr Start]	7500 hr
Life with 3h/day use [years]	3 an

• Light Technical Characteristics

Color Code	33
Color Rendering Index	62 Ra8
Color Designation	Cool White
Color Temperature	4100 K
Initial lumen	870 Lm
Design Mean Lumens	765 Lm

• Electrical Characteristics

Watts	15 W
-------	------

• Environmental Characteristics

Mercury (Hg) Content	1.4 mg
Picogram per Lumen Hour	244 p/LuHr

• Product Dimensions

Nominal Length [inch]	18
-----------------------	----

• Product Data



Product number	392076
Full product name	F15T8 CW Plus ALTO
Short product name	F15T8 CW Plus ALTO/6
Pieces per Sku	1
Skus/Case	6
Bar code on pack	046677392079
Bar code on case	50046677392074
Logistics code(s)	927875603312

PHILIPS

sense and simplicity

Dimensional drawing

G13, T8



© 2011 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2011, October 8
data subject to change