



Preheat T12

F14T12 CW 1LP

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

Product data

• General Characteristics

Base	Medium Bi-Pin [Medium Bi-Pin Fluorescent]
Base Information	Aluminum [Aluminum Base]
Bulb	T12
Rated Avg. Life [3 hr Start]	9000 hr

• Light Technical Characteristics

Color Code	33
Color Rendering Index	62 Ra8
Color Designation	Cool White
Color Temperature	4100 K
Initial lumen	710 Lm
Design Mean Lumens	590 Lm

• Electrical Characteristics

Watts	14 W
-------	------

• Product Dimensions

Nominal Length [inch]	15
-----------------------	----


• Product Data

Product number	141515
Full product name	F14T12 CW 1LP
Short product name	F14T12 CW 1LP
Pieces per Sku	1
eop_pck_cfg	30
Skus/Case	30
Bar code on pack	46677141516
Bar code on case	50046677141511
Logistics code(s)	927881003306
eop_net_weight_pp	0.001 kg


PHILIPS

sense and simplicity


Dimensional drawing



G13, T12



G13



G13, T12



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change