



Preheat T12

F20T12 D ALTO

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

Product data

• General Characteristics

Base	Medium Bi-Pin [Medium Bi-Pin Fluorescent]
Base Information	Green Base
Bulb	T12
Rated Avg. Life [3 hr Start]	9000 hr
Life with 3h/day use [years]	4 an

• Light Technical Characteristics

Color Code	54
Color Rendering Index	79 Ra8
Color Designation	Daylight [Daylight]
Color Temperature	6500 K
Initial lumen	1075 Lm
Design Mean Lumens	960 Lm

• Electrical Characteristics

Watts	20 W
-------	------

• Environmental Characteristics

Mercury (Hg) Content	1.9 mg
----------------------	--------

• Product Dimensions

Nominal Length [inch]	24
-----------------------	----


• Product Data

Product number	273284
Full product name	F20T12 D ALTO
Short product name	F20T12 D ALTO/30
Pieces per Sku	1
eop_pck_cfg	30
Skus/Case	30
Bar code on pack	46677273286
Bar code on case	50046677273281
Logistics code(s)	927883005405
eop_net_weight_pp	0.001 kg


PHILIPS

sense and simplicity


Dimensional drawing



G13, T12



G13



G13, T12



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change