



# Preheat T12

F25T12 CW

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

## Product data

### • General Characteristics

Base	Medium Bi-Pin [Medium Bi-Pin Fluorescent]
Base Information	Aluminum [Aluminum Base]
Bulb	T12
Rated Avg. Life [3 hr Start]	7500 hr

### • Light Technical Characteristics

Color Code	33
Color Rendering Index	62 Ra8
Color Designation	Cool White
Color Temperature	4100 K
Initial lumen	1900 Lm
Design Mean Lumens	1710 Lm

### • Electrical Characteristics

Watts	25 W
-------	------

### • Product Dimensions

Nominal Length [inch]	33
-----------------------	----


### • Product Data

Product number	141432
Full product name	F25T12 CW
Short product name	F25T12 CW
Pieces per Sku	1
eop_pck_cfg	30
Skus/Case	30
Bar code on pack	46677141431
Bar code on case	50046677141436
Logistics code(s)	927885003302
eop_net_weight_pp	0.001 kg


# PHILIPS

sense and simplicity


Dimensional drawing



G13, T12



G13



G13, T12



© 2012 Koninklijke Philips Electronics N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2012, August 4  
data subject to change