



Rapid Start T12

F30T12 CW RS ALTO

Philips T12 fluorescent lamps provide high performance and long life in a wide range of sizes, shapes, and types.

Product data

• General Characteristics

System Description	Rapid Start
Base	Medium Bi-Pin [Medium Bi-Pin Fluorescent]
Base Information	Green Base
Bulb	T12
Rated Avg. Life [3 hr Start]	18000 hr
Energy Saving	Not Applicable
Life with 3h/day use [years]	7 an

• Light Technical Characteristics

Color Code	33
Color Rendering Index	62 Ra8
Color Designation	Cool White
Color Temperature	4100 K
Initial lumen	2250 Lm
Design Mean Lumens	1900 Lm

• Electrical Characteristics

Watts	30 W
-------	------

• Environmental Characteristics

Mercury (Hg) Content	3.5 mg
----------------------	--------

• Product Dimensions

Nominal Length [inch]	36
-----------------------	----


• Product Data

Product number	272427
Full product name	F30T12 CW RS ALTO
Short product name	F30T12 CW RS ALTO/30
Pieces per Sku	1
eop_pck_cfg	30
Skus/Case	30
Bar code on pack	46677272425
Bar code on case	50046677272420
Logistics code(s)	927886003305
eop_net_weight_pp	0.001 kg


PHILIPS

sense and simplicity


Dimensional drawing



G13, T12



G13



G13, T12



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change