



Rapid Start T12

F30T12 D RS ALTO

Philips T12 fluorescent lamps provide high performance and long life in a wide range of sizes, shapes, and types.

Product data

• General Characteristics

System Description	Rapid Start
Base	Medium Bi-Pin [Medium Bi-Pin Fluorescent]
Base Information	Green Base
Bulb	T12
Rated Avg. Life [3 hr Start]	18000 hr
Energy Saving	Not Applicable

• Light Technical Characteristics

Color Code	54
Color Rendering Index	79 Ra8
Color Designation	Daylight [Daylight]
Color Temperature	6500 K
Initial lumen	1950 Lm
Design Mean Lumens	1700 Lm

• Electrical Characteristics

Watts	30 W
-------	------

• Product Dimensions

Nominal Length [inch]	36
-----------------------	----


• Product Data

Product number	376491
Full product name	F30T12 D RS ALTO
Short product name	F30T12 D RS ALTO/30
Pieces per Sku	1
eop_pck_cfg	30
Skus/Case	30
Bar code on pack	46677376499
Bar code on case	50046677376494
Logistics code(s)	927886005403
eop_net_weight_pp	0.001 kg


PHILIPS

sense and simplicity


Dimensional drawing



G13, T12



G13



G13, T12



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change