



Slimline T12

Slimline F36T12 CW

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data

• General Characteristics

Base	Single Pin [Single Pin Fluorescent]
Base Information	Aluminum [Aluminum Base]
Bulb	T12
Rated Avg. Life [3 hr Start]	7500 hr
Energy Saving	Energy Saving

• Light Technical Characteristics

Color Code	33
Color Rendering Index	62 Ra8
Color Designation	Cool White
Color Temperature	4100 K
Initial lumen	1850 Lm
Design Mean Lumens	1630 Lm

• Electrical Characteristics

Watts	30 W
-------	------

• Product Dimensions

Nominal Length [inch]	36
-----------------------	----

• Product Data


Product number	141408
Full product name	Slimline F36T12 CW
Short product name	F36T12 CW
Pieces per Sku	1
eop_pck_cfg	30
Skus/Case	30
Bar code on pack	46677141400
Bar code on case	50046677141405
Logistics code(s)	927887003302
eop_net_weight_pp	0.001 kg

Dimensional drawing

Dimensional drawing

FA8, T12

Product	C (Norm)	D (Max)
F36T12 30W/33 ES	-	-



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change