



Retail Sales T12

F40T12 PLANT 48 1SL

High Performance, Long Life, Environmentally-Responsible Lamps These high performance lamps are ideal for applications where high lumens, long life and high CRI are required.

Product data

• General Characteristics

Base	Medium Bi-Pin [Medium Bi-Pin Fluorescent]
Base Information	Aluminum [Aluminum Base]
Bulb	T12
Rated Avg. Life [3 hr Start]	20000 hr
Energy Saving	Not Applicable

• Light Technical Characteristics

Color Code	7
Color Designation	Plant and Aquarium
Initial lumen	1600 Lm
Design Mean Lumens	1360 Lm

• Electrical Characteristics

Watts	40 W
-------	------

• Environmental Characteristics

Mercury (Hg) Content	16.0 mg
----------------------	---------

• Product Dimensions

Nominal Length [inch]	48
-----------------------	----


• Product Data

Product number	392282
Full product name	F40T12 PLANT 48 1SL
Short product name	F40T12 PLANT 48 1SL
Pieces per Sku	1
eop_pck_cfg	6
Skus/Case	6
Bar code on pack	46677392284
Bar code on case	50046677392289
Logistics code(s)	927888000702
eop_net_weight_pp	0.375 kg


PHILIPS

sense and simplicity


Dimensional drawing



G13, T12



G13



G13, T12



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change