



# Rapid Start T12

F40T12 841 ALTO

Philips T12 fluorescent lamps provide high performance and long life in a wide range of sizes, shapes, and types.

## Product data

### • General Characteristics

Base	Medium Bi-Pin [Medium Bi-Pin Fluorescent]
Base Information	Green Base
Bulb	T12
Rated Avg. Life [3 hr Start]	20000 hr
Energy Saving	Not Applicable

### • Light Technical Characteristics

Color Code	841 [CCT of 4100K]
Color Rendering Index	82 Ra8
Color Designation	841
Color Temperature	4100 K
Initial lumen	3200 Lm
Design Mean Lumens	2970 Lm

### • Electrical Characteristics

Watts	40 W
-------	------

### • Environmental Characteristics

Mercury (Hg) Content	4.4 mg
----------------------	--------

### • Product Dimensions

Nominal Length [inch]	48
-----------------------	----

### • Footnotes

Footnotes Fluorescent/CFL	920 [Circle E- The encircled E means this bulb meets Federal minimum efficiency standards.]
---------------------------	---


### • Product Data

Product number	142638
Full product name	F40T12 841 ALTO
Short product name	F40T12 841 ALTO
Pieces per Sku	1
eop_pck_cfg	30
Skus/Case	30
Bar code on pack	46677142636
Bar code on case	50046677142631
Logistics code(s)	927888084105
eop_net_weight_pp	0.001 kg


# PHILIPS

sense and simplicity


## Dimensional drawing



G13, T12



G13



G13, T12



© 2012 Koninklijke Philips Electronics N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2012, August 4  
data subject to change