



Advantage T12

F40T12 ADV850 ALTO

Philips T12 fluorescent lamps provide high performance and long life in a wide range of sizes, shapes, and types.

Product data

• General Characteristics

Base	Medium Bi-Pin [Medium Bi-Pin Fluorescent]
Base Information	Green Base
Bulb	T12
Rated Avg. Life [3 hr Start]	24000 hr

• Light Technical Characteristics

Color Code	Advantage 850 [CCT of 5000K]
Color Rendering Index	85 Ra8
Color Designation	Advantage 850
Color Temperature	5000 K
Initial lumen	3600 Lm
Design Mean Lumens	3250 Lm

• Electrical Characteristics

Watts	40 W
-------	------

• Environmental Characteristics

Mercury (Hg) Content	4.4 mg
----------------------	--------

• Product Dimensions

Nominal Length [inch]	48
-----------------------	----


• Product Data

Product number	266437
Full product name	F40T12 ADV850 ALTO
Short product name	F40T12 ADV850 ALTO/30
Pieces per Sku	1
eop_pck_cfg	30
Skus/Case	30
Bar code on pack	46677266431
Bar code on case	50046677266436
Logistics code(s)	927888085103
eop_net_weight_pp	287.123 gr


PHILIPS

sense and simplicity


Dimensional drawing



G13, T12



G13



G13, T12



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change