



# Advantage T12

F34T12 ADV850 EW ALTO

Philips T12 fluorescent lamps provide high performance and long life in a wide range of sizes, shapes, and types.

## Product data

### • General Characteristics

Base	Medium Bi-Pin [Medium Bi-Pin Fluorescent]
Base Information	Green Base
Bulb	T12
Rated Avg. Life [3 hr Start]	24000 hr

### • Light Technical Characteristics

Color Code	Advantage 850 [CCT of 5000K]
Color Rendering Index	85 Ra8
Color Designation	Advantage 850
Color Temperature	5000 K
Initial lumen	2950 Lm
Design Mean Lumens	2655 Lm

### • Electrical Characteristics

Watts	34 W
-------	------

### • Environmental Characteristics

Mercury (Hg) Content	4.4 mg
----------------------	--------

### • Product Dimensions

Nominal Length [inch]	48
-----------------------	----


### • Product Data

Product number	142604
Full product name	F34T12 ADV850 EW ALTO
Short product name	F34T12 ADV850 EW ALTO
Pieces per Sku	1
eop_pck_cfg	30
Skus/Case	30
Bar code on pack	46677142605
Bar code on case	50046677142600
Logistics code(s)	927888185101
eop_net_weight_pp	0.001 kg


# PHILIPS

sense and simplicity


## Dimensional drawing



G13, T12



G13



G13, T12



© 2012 Koninklijke Philips Electronics N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2012, August 4  
data subject to change