



Rapid Start T12

F34T12 WW EW LL ALTO

Philips T12 fluorescent lamps provide high performance and long life in a wide range of sizes, shapes, and types.

Product data

• General Characteristics

System Description	Rapid Start
Base	Medium Bi-Pin [Medium Bi-Pin Fluorescent]
Base Information	Green Base
Bulb	T12
Rated Avg. Life [3 hr Start]	24000 hr
Energy Saving	Energy Saving

• Light Technical Characteristics

Color Code	29
Color Rendering Index	53 Ra8
Color Designation	Warm White
Color Temperature	3000 K
Initial lumen	2700 Lm
Design Mean Lumens	2350 Lm

• Electrical Characteristics

Watts	34 W
-------	------

• Environmental Characteristics

Mercury (Hg) Content	4.4 mg
----------------------	--------

• Product Dimensions

Nominal Length [inch]	48
-----------------------	----


• Product Data

Product number	142521
Full product name	F34T12 WW EW LL ALTO
Short product name	F34T12 WW EW LL ALTO
Pieces per Sku	1
eop_pck_cfg	30
Skus/Case	30
Bar code on pack	46677142520
Bar code on case	50046677142525
Logistics code(s)	927888302901
eop_net_weight_pp	0.001 kg


PHILIPS

sense and simplicity


Dimensional drawing



G13, T12



G13



G13, T12



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change