



Slimline T12

Slimline F60T12 CW ALTO 1LP

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data

• General Characteristics

Base	Single Pin [Single Pin Fluorescent]
Base Information	Green Base
Bulb	T12
Rated Avg. Life [3 hr Start]	12000 hr

• Light Technical Characteristics

Color Code	33
Color Rendering Index	82 Ra8
Color Designation	Cool White
Initial lumen	3310 Lm
Design Mean Lumens	3050 Lm

• Electrical Characteristics

Watts	50 W
-------	------

• Environmental Characteristics

Mercury (Hg) Content	6.8 mg
----------------------	--------

• Product Dimensions

Nominal Length [inch]	60
-----------------------	----

• Product Data


Product number	234302
Full product name	Slimline F60T12 CW ALTO 1LP
Short product name	F60T12 CW ALTO 1LP
Pieces per Sku	1
eop_pck_cfg	15
Skus/Case	15
Bar code on pack	46677234300
Bar code on case	50046677234305
Logistics code(s)	927891103301
eop_net_weight_pp	0.001 kg

Dimensional drawing

Dimensional drawing

FA8, T12

Product	C (Norm)	D (Max)
F60T12 50W/33 ALTO®	-	-



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change