



Slimline T12

Slimline F72T12 CW ALTO

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data

• General Characteristics

Base	Single Pin [Single Pin Fluorescent]
Base Information	Green Base
Bulb	T12
Rated Avg. Life [3 hr Start]	12000 hr
Energy Saving	Not Applicable

• Light Technical Characteristics

Color Code	33
Color Rendering Index	62 Ra8
Color Designation	Cool White
Color Temperature	4100 K
Initial lumen	4450 Lm
Design Mean Lumens	3900 Lm

• Electrical Characteristics

Watts	56 W
-------	------

• Environmental Characteristics

Mercury (Hg) Content	6.8 mg
----------------------	--------

• Product Dimensions

Nominal Length [inch]	72
-----------------------	----

• Product Data


Product number	369892
Full product name	Slimline F72T12 CW ALTO
Short product name	F72T12 CW ALTO/15
Pieces per Sku	1
eop_pck_cfg	15
Skus/Case	15
Bar code on pack	46677369897
Bar code on case	50046677369892
Logistics code(s)	927893003308
eop_net_weight_pp	0.001 kg

Dimensional drawing

Dimensional drawing

FA8, T12

Product	C (Norm)	D (Max)
F72T12.56W/33 ALTO	-	-



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change