



Slimline T12

Slimline F72T12 D ALTO

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data

• General Characteristics

Base	Single Pin [Single Pin Fluorescent]
Base Information	Green Base
Bulb	T12
Rated Avg. Life [3 hr Start]	12000 hr
Energy Saving	Not Applicable

• Light Technical Characteristics

Color Code	54
Color Rendering Index	79 Ra8
Color Designation	Daylight [Daylight]
Color Temperature	6500 K
Initial lumen	3800 Lm
Design Mean Lumens	3350 Lm

• Electrical Characteristics

Watts	56 W
-------	------

• Environmental Characteristics

Mercury (Hg) Content	6.8 mg
----------------------	--------

• Product Dimensions

Nominal Length [inch]	72
-----------------------	----

• Product Data


Product number	369850
Full product name	Slimline F72T12 D ALTO
Short product name	F72T12 D ALTO/15
Pieces per Sku	1
eop_pck_cfg	15
Skus/Case	15
Bar code on pack	46677369859
Bar code on case	50046677369854
Logistics code(s)	927893005403
eop_net_weight_pp	0.001 kg

Dimensional drawing

Dimensional drawing

FA8, T12

Product	C (Norm)	D (Max)
F72T12.56W/54 ALTO	-	-



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change