



# High Output T12

F96T12 HO/EW ALTODX 1LP

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

## Product data

### • General Characteristics

Base	R17d [Recessed Double Contact Bay (RDC Bay-Fluorescent)]
Base Information	Green Base
Bulb	T12
Rated Avg. Life [3 hr Start]	12000 hr
Energy Saving	Energy Saving

### • Light Technical Characteristics

Color Code	57
Color Rendering Index	82 Ra8
Color Temperature	6500 K
Initial lumen	5615 Lm
Design Mean Lumens	5000 Lm

### • Electrical Characteristics

Watts	95 W
-------	------

### • Environmental Characteristics

Mercury (Hg) Content	6.8 mg
----------------------	--------

### • Product Dimensions

Nominal Length [inch]	96
-----------------------	----


### • Product Data

Product number	214718
Full product name	F96T12 HO/EW ALTODX 1LP
Short product name	F96T12 HO/EW ALTODX 1LP
Pieces per Sku	1
eop_pck_cfg	15
Skus/Case	15
Bar code on pack	46677214715
Bar code on case	50046677214710
Logistics code(s)	927894605701
eop_net_weight_pp	0.001 kg


# PHILIPS

sense and simplicity

## Dimensional drawing



T12 Recessed Double Contact  
R17d, T12



T12 Recessed Double Contact  
R17d, T12



© 2012 Koninklijke Philips Electronics N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2012, August 4  
data subject to change