



High CRI T12

F96T12 HO ALTODX

Philips T12 High CRI Lamps are energy-efficient lighting solutions and provide excellent color consistency over the life of the lamp.

Product data

• General Characteristics

Base	R17d [Recessed Double Contact Bay (RDC Bay-Fluorescent)]
Base Information	Green Base
Bulb	T12
Rated Avg. Life [3 hr Start]	12000 hr

• Light Technical Characteristics

Color Code	57
Color Rendering Index	82 Ra8
Color Temperature	6500 K
Initial lumen	6750 Lm
Design Mean Lumens	5800 Lm

• Electrical Characteristics

Watts	110 W
-------	-------

• Environmental Characteristics

Mercury (Hg) Content	6.8 mg
----------------------	--------

• Product Dimensions

Nominal Length [inch]	96
-----------------------	----


• Product Data

Product number	214890
Full product name	F96T12 HO ALTODX
Short product name	F96T12/DX/H/ALTO 15PK
Pieces per Sku	1
eop_pck_cfg	15
Skus/Case	15
Bar code on pack	46677214890
Bar code on case	50046677214895
Logistics code(s)	927894705701
eop_net_weight_pp	0.001 kg


PHILIPS

sense and simplicity

Dimensional drawing



T12 Recessed Double Contact
R17d, T12



T12 Recessed Double Contact
R17d, T12



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change