



Slimline T12

Slimline F96T12 C50

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data

• General Characteristics

| | |
|------------------------------|-------------------------------------|
| Base | Single Pin [Single Pin Fluorescent] |
| Base Information | Aluminum [Aluminum Base] |
| Bulb | T12 |
| Rated Avg. Life [3 hr Start] | 12000 hr |
| Energy Saving | Not Applicable |

• Light Technical Characteristics

| | |
|-----------------------|--------------|
| Color Code | 47 |
| Color Rendering Index | 92 Ra8 |
| Color Designation | Colortone 50 |
| Color Temperature | 5000 K |
| Initial lumen | 4650 Lm |
| Design Mean Lumens | 3795 Lm |

• Electrical Characteristics

| | |
|-------|------|
| Watts | 75 W |
|-------|------|

• Environmental Characteristics

| | |
|----------------------|---------|
| Mercury (Hg) Content | 20.0 mg |
|----------------------|---------|

• Product Dimensions

| | |
|-----------------------|----|
| Nominal Length [inch] | 96 |
|-----------------------|----|

• Product Data


| | |
|--------------------|---------------------|
| Product number | 341701 |
| Full product name | Slimline F96T12 C50 |
| Short product name | F96T12 C50/15 |
| Pieces per Sku | 1 |
| eop_pck_cfg | 15 |
| Skus/Case | 15 |
| Bar code on pack | 46677341701 |
| Bar code on case | 50046677341706 |
| Logistics code(s) | 927895004702 |
| eop_net_weight_pp | 0.001 kg |

Dimensional drawing

Dimensional drawing

FA8, T12

| Product | C (Norm) | D (Max) |
|---------------|----------|---------|
| F96T12 75W/47 | - | - |



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change