



# High CRI T12

F96T12 DX ALTO TG

Philips T12 High CRI Lamps are energy-efficient lighting solutions and provide excellent color consistency over the life of the lamp.

## Product data

### • General Characteristics

|                              |                                     |
|------------------------------|-------------------------------------|
| Base                         | Single Pin [Single Pin Fluorescent] |
| Base Information             | Green Base                          |
| Bulb                         | T12                                 |
| Rated Avg. Life [3 hr Start] | 12000 hr                            |
| Energy Saving                | Not Applicable                      |

### • Light Technical Characteristics

|                       |                 |
|-----------------------|-----------------|
| Color Code            | 57              |
| Color Rendering Index | 84 Ra8          |
| Color Designation     | Daylight Deluxe |
| Color Temperature     | 6500 K          |
| Initial lumen         | 4775 Lm         |
| Design Mean Lumens    | 4200 Lm         |

### • Electrical Characteristics

|       |      |
|-------|------|
| Watts | 75 W |
|-------|------|

### • Environmental Characteristics

|                      |        |
|----------------------|--------|
| Mercury (Hg) Content | 6.8 mg |
|----------------------|--------|

### • Product Dimensions

|                       |    |
|-----------------------|----|
| Nominal Length [inch] | 96 |
|-----------------------|----|

### • Product Data


|                    |                   |
|--------------------|-------------------|
| Product number     | 162974            |
| Full product name  | F96T12 DX ALTO TG |
| Short product name | F96T12 DX ALTO TG |
| Pieces per Sku     | 1                 |
| eop_pck_cfg        | 15                |
| Skus/Case          | 15                |
| Bar code on pack   | 46677162979       |
| Bar code on case   | 50046677162974    |
| Logistics code(s)  | 927895005719      |
| eop_net_weight_pp  | 0.001 kg          |

## Dimensional drawing

## Dimensional drawing

### FA8, T12

| Product            | C (Norm) | D (Max) |
|--------------------|----------|---------|
| F96T12 75W/57 ALTO | -        | -       |



© 2012 Koninklijke Philips Electronics N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2012, August 4  
data subject to change