



Slimline 800 Series T12

F96T12 75W 850 ALTO

Philips leads the industry with the lowest level mercury technology. Reducing the mercury level (source reduction) during the manufacturing phase is essential to creating products that are less harmful to the environment.

Product data

• General Characteristics

Base	Single Pin [Single Pin Fluorescent]
Base Information	Green Base
Bulb	T12
Rated Avg. Life [3 hr Start]	12000 hr
Energy Saving	Not Applicable

• Light Technical Characteristics

Color Code	850 [CCT of 5000K]
Color Rendering	85 Ra8
Index	
Color Designation	850
Color Temperature	5000 K
Initial lumen	6500 Lm
Design Mean Lumens	6125 Lm

• Electrical Characteristics

Watts	75 W
-------	------

• Environmental Characteristics

Mercury (Hg) Content	6.8 mg
----------------------	--------

• Product Dimensions

Nominal Length [inch]	96
-----------------------	----

• Product Data


Product number	142760
Full product name	F96T12 75W 850 ALTO
Short product name	F96T12 75W 850 ALTO
Pieces per Sku	1
eop_pck_cfg	15
Skus/Case	15
Bar code on pack	46677142766
Bar code on case	50046677142761
Logistics code(s)	927895085009
eop_net_weight_pp	0.001 kg

Dimensional drawing

Dimensional drawing

FA8, T12

Product	C (Norm)	D (Max)
F96T12 75W/850 ALTO	-	-



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change