



High Output T12

F96T12 CW ALTO HO-O

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

Product data

• General Characteristics

Base	R17d [Recessed Double Contact Bay (RDC Bay-Fluorescent)]
Base Information	Green Base
Bulb	T12
Rated Avg. Life [3 hr Start]	12000 hr
Energy Saving	Not Applicable

• Light Technical Characteristics

Color Code	33
Color Rendering Index	62 Ra8
Color Designation	Cool White
Color Temperature	4100 K
Initial lumen	8800 Lm
Design Mean Lumens	7650 Lm

• Electrical Characteristics

Watts	110 W
-------	-------

• Environmental Characteristics

Mercury (Hg) Content	6.8 mg
----------------------	--------

• Product Dimensions

Nominal Length [inch]	96
-----------------------	----

• Footnotes

Footnotes Fluorescent/CFL	223 [Meets the National Energy Policy Act of 1992 exemption for outdoor or cold temperature applications only. (223)]
---------------------------	---


• Product Data

Product number	381764
Full product name	F96T12 CW ALTO HO-O
Short product name	F96T12 CW ALTO HO-O/15
Pieces per Sku	1
eop_pck_cfg	15
Skus/Case	15
Bar code on pack	46677381769
Bar code on case	50046677381764
Logistics code(s)	927895203323
eop_net_weight_pp	0.001 kg


PHILIPS

sense and simplicity

Dimensional drawing



T12 Recessed Double Contact
R17d, T12



T12 Recessed Double Contact
R17d, T12



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change