



# High Output T12

F96T12 D HO-O ALTO

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

## Product data

### • General Characteristics

Base	R17d [Recessed Double Contact Bay (RDC Bay-Fluorescent)]
Base Information	Green Base
Bulb	T12
Rated Avg. Life [3 hr Start]	12000 hr
Energy Saving	Not Applicable

### • Light Technical Characteristics

Color Code	54
Color Rendering Index	79 Ra8
Color Designation	Daylight [Daylight]
Color Temperature	6500 K
Initial lumen	7800 Lm
Design Mean Lumens	6800 Lm

### • Electrical Characteristics

Watts	110 W
-------	-------

### • Environmental Characteristics

Mercury (Hg) Content	6.8 mg
----------------------	--------

### • Product Dimensions

Nominal Length [inch]	96
-----------------------	----

### • Footnotes

Footnotes Fluorescent/CFL	223 [Meets the National Energy Policy Act of 1992 exemption for outdoor or cold temperature applications only. (223)]
---------------------------	---


### • Product Data

Product number	381774
Full product name	F96T12 D HO-O ALTO
Short product name	F96T12 D HO-O ALTO/15
Pieces per Sku	1
eop_pck_cfg	15
Skus/Case	15
Bar code on pack	46677381776
Bar code on case	50046677381771
Logistics code(s)	927895205408
eop_net_weight_pp	0.694 kg


# PHILIPS

sense and simplicity

## Dimensional drawing



T12 Recessed Double Contact  
R17d, T12



T12 Recessed Double Contact  
R17d, T12



© 2012 Koninklijke Philips Electronics N.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2012, August 4  
data subject to change