



PL-C Cluster 2-Pin Base 15mm Tube

PL-C15mm 22W/827 1CT

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Product data

• General Characteristics

Base	GX32d-2
Bulb	PL-C
Rated Avg. Life [3 hr Start]	10000 hr
Energy Saving	Energy Saving

• Light Technical Characteristics

Color Code	827 [CCT of 2700K]
Color Rendering Index	82 Ra8
Color Temperature	2700 K
Initial lumen	1200 Lm
Design Mean Lumens	995 Lm

• Electrical Characteristics

Watts	22 W
-------	------

• Product Dimensions

Max Overall Length (MOL) - C	6.00 (max) in
------------------------------	---------------

• Product Data

Product number	241687
Full product name	PL-C15mm 22W/827 1CT
Short product name	PL-C 15MM/22W/27 40PK
Pieces per Sku	1
Skus/Case	40
Bar code on pack	46677241681
Bar code on case	50046677241686
Logistics code(s)	927897482702
eop_net_weight_pp	0.086 kg