



PL-C Cluster 2-Pin Base 15mm Tube

PL-C15mm 28W/827 GX32d-3 1CT

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.

Product data

• General Characteristics

Base	GX32d-3
Bulb	PL-C
Rated Avg. Life [3 hr Start]	10000 hr
Energy Saving	Energy Saving

• Light Technical Characteristics

Color Code	827 [CCT of 2700K]
Color Rendering Index	82 Ra8
Color Temperature	2700 K
Initial lumen	1600 Lm
Design Mean Lumens	1325 Lm

• Electrical Characteristics

Watts	28 W
-------	------

• Product Dimensions

Max Overall Length (MOL) - C	6.81 (max) in
------------------------------	---------------

• Product Data

Product number	241695
Full product name	PL-C15mm 28W/827 GX32d-3 1CT
Short product name	28W/827 GX32d-3 1CT
Pieces per Sku	1
Skus/Case	40
Bar code on pack	046677241698
Bar code on case	50046677241693
Logistics code(s)	927897882702