



Appliance T8

F14T8 CW 15

Energy Savings, extra long life, extra low mercury T8 lamps offer high energy savings, superior lumen output, and long life in an environmentally responsible lamp.

Product data

• General Characteristics

Base	Medium Bi-Pin [Medium Bi-Pin Fluorescent]
Base Information	Aluminum [Aluminum Base]
Bulb	T8
Rated Avg. Life [3 hr Start]	7500 hr

• Light Technical Characteristics

Color Code	33
Color Rendering Index	62 Ra8
Color Designation	Cool White
Color Temperature	4100 K
Initial lumen	700 Lm
Design Mean Lumens	595 Lm

• Electrical Characteristics

Watts	14 W
-------	------

• Environmental Characteristics

Mercury (Hg) Content	16 mg
----------------------	-------

• Product Dimensions

Nominal Length [inch]	15
-----------------------	----


• Product Data

Product number	259143
Full product name	F14T8 CW 15
Short product name	F14T8 CW 15
Pieces per Sku	1
eop_pck_cfg	24
Skus/Case	24
Bar code on pack	46677259143
Bar code on case	50046677259148
Logistics code(s)	928075003301
eop_net_weight_pp	0.001 kg


PHILIPS

sense and simplicity


Dimensional drawing



G13, T8



G13



G13, T8



© 2012 Koninklijke Philips Electronics N.V.
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com/lighting

2012, August 4
data subject to change