



# Energy Saver Reflectors

14W EL/A R20 1CT

Looking for an energy saver that doesn't look like one? The Philips EnergySaver family provides energy efficient lighting options that don't just provide similar light as your standard incandescent light bulb, they also have the same classic shapes. Philips Energy Saver reflector flood compact fluorescents reduce operating costs without sacrificing light quality compared to incandescent equivalents. With dimmable and hard glass options, they are ideal for recessed and track lighting indoors and outdoors.

## Product data

### • General Characteristics

Base	Medium [Single Contact Medium Screw]
Bulb	EL/A R20
Rated Avg. Life [3 hr Start]	8000 hr
Energy Saving	Energy Saving

### • Light Technical Characteristics

Color Rendering Index	82 Ra8
Color Temperature	2700 K
Initial lumen	500 Lm

### • Electrical Characteristics

Watts	14 W
-------	------

### • Environmental Characteristics

Mercury (Hg) Content	3 mg
----------------------	------

### • Product Dimensions

Max Overall Length (MOL) - C	4.7 (max) in
------------------------------	--------------

### • Product Data

Product number	157016
Full product name	14W EL/A R20 1CT
Short product name	EL/A R20 14W
Pieces per Sku	1
Skus/Case	6
Bar code on pack	46677157012
Bar code on case	50046677157017
Logistics code(s)	929695567903
eop_net_weight_pp	0.001 kg

# PHILIPS

sense and simplicity