



Energy Saver Decoratives

9W EL/A G25 1CT

Philips Energy Saver Decorative CFLs provide energy savings and reduce operating costs without sacrificing quality of light compared to incandescent equivalents.

Product data

• General Characteristics

Base	Medium [Single Contact Medium Screw]
Bulb	EL/A G25
Rated Avg. Life [3 hr Start]	8000 hr
Energy Saving	Energy Saving

• Light Technical Characteristics

Color Rendering Index	82 Ra8
Color Temperature	2700 K
Initial lumen	500 Lm

• Electrical Characteristics

Watts	9 W
-------	-----

• Environmental Characteristics

Mercury (Hg) Content	2.8 mg
----------------------	--------

• Product Dimensions

Max Overall Length (MOL) - C	4.4 (max) in
------------------------------	--------------

• Product Data

Product number	157180
Full product name	9W EL/A G25 1CT
Short product name	9W EL/A G25 1CT
Pieces per Sku	1
eop_pck_cfg	6
Skus/Case	6
Bar code on pack	46677157180
Bar code on case	50046677157185
Logistics code(s)	929695568103
eop_net_weight_pp	0.001 kg