



Energy Saver Dimmables

20W Med EL/A R40 Dim ALTO 1CT

Looking for an energy saving light bulb that can dim? The Philips EnergySaver family of dimmable light bulbs provide energy efficient lighting options that don't just provide similar light as your standard incandescent light bulb, they also have the same classic shapes. Try the Philips EnergySavers and see how they truly provide advanced lighting designed around your needs.

Product data

• General Characteristics

Base	Medium [Single Contact Medium Screw]
Bulb	EL/A R40
RatedAvgLife(See Family Notes)	8000 hr
Energy Saving	Energy Saving
Estimated Energy Cost/YR	2.41 \$
Life with 3h/day use [years]	7.3 an

• Light Technical Characteristics

Color Code	827 [CCT of 2700K]
Color Temperature	2830 K
Initial lumen	900 Lm

• Electrical Characteristics

Watts	20 W
-------	------

• Product Data

Product number	137083
Full product name	20W Med EL/A R40 Dim ALTO 1CT
Short product name	EL/A R40 20W DIMM REFLECTOR
Pieces per Sku	1
eop_pck_cfg	6
Skus/Case	6
Bar code on pack	46677137083
Bar code on case	50046677137088
Logistics code(s)	929737366101
eop_net_weight_pp	161.000 gr

PHILIPS

sense and simplicity