



Incandescent Lamps

Watts	Bulb Base	Product Number	Symbols, Footnotes	Ordering Code	Pkg. Qty.†	Volts	Description	Class Filament	LCL (In.)	MOL (In.)	Rated Avg. Life (Hrs.)(93)	Approx. MBCP*	Lumens	Life Years (446)	Energy Cost (445)	Color Temp. (K)
-------	-----------	----------------	--------------------	---------------	------------	-------	-------------	----------------	-----------	-----------	----------------------------	---------------	--------	------------------	-------------------	-----------------

Incandescent Lamps by Wattage

FTC REQUIREMENTS

1.5	T3	Cand.	▲†*	BC1.5T3	4.5	24	Clear Flashlight	B, C-6	2	30			17	0.0	\$0.18		
4	C7	Cand.	▲*	BC4C7 12/2	120	24	Clear Night Light	B, C-7A	2½	3000			16	2.7	\$0.48		
			▲	BC4C7/4 12/4	120	48	Clear Night Light	B, C-7A	2½	3000			16	2.7	\$0.48		
			▲*	BC4C7/W 12/2	120	24	White Night Light	B, C-7A	2½	3000			14	2.7	\$0.48		
			▲†	BC4C7/4	120	48	Clear Night Light	B, C-7A	2½	3000			16	2.7	\$0.48		
	T5	Wedge		†	BC4T5/G/TP	12	24	Transparent Green Landscape	B, C-2R	1½	300				0.3	\$0.48	
				†	BC4T5/A/TP	12	24	Transparent Amber Landscape	B, C-2R	1½	300				0.3	\$0.48	
				†	BC4T5/R/TP	12	24	Transparent Red Landscape	B, C-2R	1½	300				0.3	\$0.48	
†				BC4T5/B/TP	12	24	Transparent Blue Landscape	B, C-2R	1½	300				0.3	\$0.48		
6	S6	Cand.		6S6	120-130	48	Clear Indicator	B, C-7A	1½	1500			39	1.4	\$0.72		
			▲†	BC6S6	12	24	Clear Indicator Light	B, C-2V	2	1500			50	1.4	\$0.72		
			▲†	BC6S6	120	24	Clear Indicator Light	B, C-7A	2	1500			40	1.4	\$0.72		
7	C7	Cand.	▲	7C7	120-130	24	Clear Indicator	B, C-7A	2½	3000			45	2.7	\$0.84		
			▲*	BC7C7/W 12/2	120	24	White Night Light	B, C-7A	2½	3000			35	2.7	\$0.84		
			▲†	BC7C7/4	120	96	Clear Night Light	B, C-7A	2½	3000			45	2.7	\$0.84		
			▲†	BC7C7/W	120	48	White Night Light	B, C-7A	2½	3000			35	2.7	\$0.84		
7.5	S11	Med.	▲†	BC7½S11	120-130	12	Clear Night Light	B, C-7A	2½	1400			45	1.3	\$0.90		
			▲†	BC7½S11	120	6	White Night Light	B, C-7A	2½	1400			35	1.3	\$0.90		
10	S11	Inter.	▲†	BC10S11IN	120	12	Clear Appliance	B, C-7A/ CC-2V	3	1500				1.4	\$1.20		
11	S8	S.C. Bay	†	BC118/SC/TP	12	24	Clear Landscape	B, C-2R	2	700			180	0.6	\$1.32		
	S14	Med.	†	BC11S14/F 130V 6/IPK	130	6		B, C-9	3½	3000			70	2.7	\$1.32		
			†	BC11S14/CL 130V 6/IPK	130	6	Clear Sign	B, C-9	3½	3000			70	2.7	\$1.32		
				11S14 120/130V 24/I	120-130	24		B, C-9	3½	3000			75	2.7	\$1.32		
13	S8	S.C. Bay	†*	BC93 12V 12/2	12	24	Clear Miniature	B, C-6	2	700				0.6	\$1.57		
15	A15	Med.	▲	15A15/CL	120-130	60	Clear	B, C-9	2½	3½	2500			110	2.3	\$1.81	
			▲	15AWL 12/2	120	24	Soft White Long Life	B, C-9	3½	3000			115	2.7	\$1.81		
	T6	Cand.	▲	15T6	120	24	Clear Switchboard	B, C-7A	3¼	2000			110	1.8	\$1.81		
			(63)▲	15T6	140-150	24	Clear Switchboard	B, C-7A	3¼	2000			100	1.8	\$1.81		
			(63)▲†	BC15T6	140-150	24	Exit Sign	B, C-7A	3	2000			100	1.8	\$1.81		
			▲†	BC15T6C/TP	120	12	Clear Showcase	B, C-7A	3	1500			110	1.4	\$1.81		
T7	Cand.	(4)†	BC15T7C	120	6	Clear Showcase	B, C-7A	2½	1000			110	0.9	\$1.81			
		(4)▲†	BC15T7N 120V	120	6	Clear Appliance	B, C-7A	2½	1000			100	0.9	\$1.81			
T10	Med.	▲†	BC15T10 6/I	120	6	Clear Showcase	B, C-9	5½	2500			120					
20	T6½	Inter.		20T6½F	120	24	Frost Exit Sign	B, C-8	5½	5000			150	4.6	\$2.41		
			†	BC20T6½N/CL	120	6	Clear Exist Sign	B, C-8	5½	3000			160	2.7	\$2.41		

For the most current product information, go to the e-catalog on www.philips.com
Incandescent symbols and footnotes located on page 132

