

INCANDESCENT LAMPS

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.†	Description	Class Filament	LCL (In.)	MOL (In.)	Rated Avg. Life (Hrs.) (93)	Approx. MBCP*	Lumens
50	ER30	Med.	I4355-2	▲ \$ (87)	50ER30	120-130	24	Elliptical Reflector	C, CC-6		6%	2000		360
	PAR36	M.P.	29603-8		50PAR36/WFL	12	12	Compact Wide Flood	C, C-6		2%	2000		
			22859-3		50PAR36/NSP	12	12	Compact Narrow Spot	C, C-6		2%	2000		
	R20	Med.+++	22082-2	▲ X(87)	50R20 12/I	130	12	Lt. Frost Reflector	C, CC-6		3%	2000		380
		Med.	20187-1	▲ (87)	50R20/TG 12/I	120	12	TuffGuard Coated Reflector Lamp	C, CC-6		3%	2000		380
		Med.	26635-3	▲ X(19,87)	50R20/PK	120	60	Pink Reflector	C, CC-6		3%	2000		
		Med.+++	I6755-1	▲ X(87)	50R20/LL 12/I	120	12	Frost Long Life Reflector	C, CC-6		3%	2500		385
		Med.+++	I4019-4	X(87)	50R20/FL 12/I PRO	130	12	Frost ProPack Reflector	C, CC-6		3%	2000		385
		Med.	I3797-5	▲ (87)	50R20/FL/NTL 12/I	120	12	Natural Light Reflector	C, CC-6		3%	2000		265
		Med.	I6709-8	▲ (19,87)	50R20/Agro 12/I	120	12	Agro-Lite Plant Light	C, CC-6		3%	2000		
50 100 150	A21	3 Ct. Med.	36671-6	▲ (8)	50/150A/W 12/I	120	12	Soft White 3-Way	C, 2CC-8		5%	1200		610 1510 2120
			31739-6	▲ (8)	50/150A/STP/PK 8/I	120	8	Pink Softone Pastel®	C, 2CC-8		5%	1200		550 1310 1860
			I3564-0	▲ (8)	50/150A/NTL 12/I	120	12	Natural Light Reflector	C, 2CC-6		5%	1200		490 1250 1740
			I6948-2	▲ (8)	50/150A/WL 12/I	120	12	Soft White Long Life 3-Way	C, 2CC-8		5%	1750		575 1440 2015
			32359-2	▲ □ (8)	50/150A/DL 12/I	120	12	Director® 3-Way	C, 2CC-8		5%	1200		530 1260 1790
50 200 250	A21	3 Ct. Med.	I6949-0	▲ (8)	50/250A/WL 12/I	120	12	Soft White Long Life 3-Way	C, 2CC-8		5%	1750		575 3120 3695
52	A19	Med.	22237-2	▲ ✓	60A-52A/EW	120	48	Frost Econ-o-watt	C, CC-6		4%	1000		700
			22239-8	▲ \$	60A-52A/EW	130	48	Frost Econ-o-watt	C, CC-6		4%	1000		680
			I4999-6	▲ \$	60A-52A/99/EW	120-130	48	Frost Econ-o-watt Extended Service Ratings @ 120V =49W	C, CC-6		4%	2000 3400		660 570
57	A19	Med.*	21497-3	▲	57A 12/4	120	48	Frost	C, CC-6		4%	1000		850
			21464-3		57A 120/I PRO	130	120	Frost ProPack	C, CC-6		4%	1000		850
			21448-6	▲	57A	120	48	Frost	C, CC-6		4%	1000		850
			21466-8	▲	57A	130	48	Frost	C, CC-6		4%	1000		850
			21463-5	▲	57A/CL	130	48	Clear	C, CC-6		4%	1000		850
			21465-0		57A/CL 120/I PRO	130	120	Clear ProPack	C, CC-6		4%	1000		920
			21452-8	▲	57A/CL/LL/TP 12/2	120	24	Clear Long Life	C, CC-6		4%	1500		810
			21449-4	▲	57A/W/TP 24/4	120	96	Soft White	C, CC-6		4%	1000		780
			21498-1	▲	57A/W/TP 12/4	120	48	Soft White	C, CC-6		4%	1000		780
			21451-0	▲	57A/WL 24/4	120	96	Soft White Longer Life	C, CC-6		4%	1500		750
			21499-9	▲	57A/WL 12/4 TP	120	48	Soft White Longer Life	C, CC-6		4%	1500		750
			21500-4	▲	57A/WL 120/4 TP	120	480	Soft White Longer Life	C, CC-6		4%	1500		750

For the most current product information, go to the e-catalog on www.philips.com
Incandescent symbols and footnotes located on page 51

