



Dependable Power for Any Application

Product Datasheet

460 Δ Primary Volts - 230Y/133 Secondary Volts - 3 \emptyset Drive Isolation Transformer - Three Phase

Catalog #: DTGA0404S



PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 3R with optional Weather Shield
- Aluminum foil windings
- Copper bus bar terminations
- Wound/Distributed core construction
- Covered under Acme's 10 year limited warranty
- Optional Thermal Switch - part # PL79900
- Optional wall mounting kit - part # PL79912

BENEFITS

- Copper terminations for trouble free operation
- Wound Core and Strip Winding for Low Losses
- Electrostatic shield for enhanced protection
- Full capacity taps on all units

UL STANDARD

UL 1561

CSA STANDARD

C22.2 No. 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

kVA:	40.00
Primary Voltage:	460Δ
Secondary Voltage:	230Y/133
Frequency:	60 Hz
ANFC Taps:	2
BNFC Taps:	2
Taps % Steps:	2.5%
Max Temperature Rise:	150°C
UL Insulation Class:	220°C

PRODUCT MEASUREMENTS

Height (In./cm):	25.5 (64.8)
Width (In./cm):	24.39 (61.9)
Depth (In./cm):	19.37 (49.2)

CONFIGURATION

Construction Type:	Ventilated
Mounting Type:	Floor
Weather Shield:	WSA1
Wiring Diagram:	38

PACKAGING

Ship Weight (Lbs/Kg):	395 (179.0)
-----------------------	-------------

COMPLIANCES

UL Standard:	UL 1561
UL Listed:	File E12547
CSA Standard:	C22.2 No. 47
CSA Listed:	LR7357-32
Warranty:	Acme Electric Warranty Card www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf