

# Copper Pathlyte (CUL7) Specification Sheet

Project Name:	Location:	MFG: Philips Hadco
Fixture Type:	Catalog No.:	Qty:

## Ordering Guide

Example: CUL7 S7 \_

<b>Product Code</b>	CUL7	Copper Pathlyte	
<b>Mounting</b>	S7	Mounting Stake	*1
<b>Finish</b>	_	Natural Copper	*2

\*1 Mounting stake option available only with Natural Copper Pathlyte.

\*2 When ordering Natural Copper, product code will read as CUL7.

## Specifications

### HOUSING:

Spun solid copper roof with copper stem. Machined copper threaded adapter for tool-less relamping. 1/2" NPS male threads to screw onto accessory mounting stake or junction box, sold separately.

### FINISH:

Natural Copper is bright polished, untreated copper. Color will age naturally to a fine dark copper patina.

### OPTICAL ASSEMBLY:

Frosted tempered glass lens. Reflective white powdercoat on underside of roof.

### LAMPING:

20W maximum T3 bi-pin lamp. Lamp is included with fixture. Lower wattage lamps are acceptable.

### ELECTRICAL ASSEMBLY:

Bi-pin socket type (G4) with 250° C high temperature teflon coated wire leads. 12 Volt fixture is pre-wired with 3-ft pigtail of 18-2 AWG, 105° C, SPT-1W wire. Low voltage quick connector, catalog #LVC3 included for easy hook-up to the low voltage supply cable, not included. 12 Volt system requires remote transformer, not included.

### WARRANTY:

Ten-year limited warranty.

### CERTIFICATIONS:

ETL listed to U.S. safety standards for wet locations. cETL listed to Canadian safety standards for wet locations. Manufactured to ISO 9001:2008 Standards.

### Height :

19 1/8" (485 mm)

### Width:

6" (152mm)

### Max. Weight:

3.3 lb