

## SPECIALTY LAMPS

Product Number	Description	Watts	Volts	Nom. Length (mm)	Diameter (mm)
----------------	-------------	-------	-------	------------------	---------------

### MEDIUM PRESSURE METAL HALIDE LAMPS

44431-5	HPM 10/B	400	125	112	17
30832-0	HPM 12	460	120	98	21
44440-6	HPM 13	1000	125	147	27
30831-2	HPM 15	1950	240	203	32
30829-6	HPM 17	2000	243	175	27
30828-8	HPM 19	2000	200	179	27
30827-0	HPM 20	2900	350	236	27
44439-8	HPM 20C	2900	350	210	27
44448-9	HPA 4005	400	125	118	18

Product Number	Description	Watts	Volts	Max. Length (mm)	Width or Diameter (mm)
----------------	-------------	-------	-------	------------------	------------------------

### LOW PRESSURE PULSED XENON DISCHARGE LAMPS

30750-4	XOP 7 O/F	750	52	241	16.2
30749-6	XOP 15 O/F	1500	105	395	16.2

For the most current product information, go to the e-catalog on [www.philips.com](http://www.philips.com)

