

Incandescent

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg Qty*	Description	Class, Filament	LCL (In.)	MOL (In.)	Rated Avg. Life, Hrs (93)	Approx. MBCP	Lumens		
350	PAR-56	M.P.	22904-7		350PAR56/SP	75	8	Train Light	C, CC-8		4 1/2	500	185,000	6200		
375	BR-40	Med. Skt.	14342-0	(19, 31, 37, 38)	375BR40	120	24	Reflector Infrared Lt. Frost Industrial	C, C-7A		7 3/4	5000				
	R-40	Med. Skt.	14574-8	(11, 31, 37, 89)	375R40/I	120	24	Clear Reflector Infrared Industrial	C, C-7A		7 3/4	5000				
400	G-30	Med.	37443-9	■ X (12, 22)	400G/FL	120-130	60	Clear Floodlight	C, C-7A	3	5 1/4	800		6280		
			14461-8	(12, 22)	400G/FL	120-130	60	Clear Floodlight	C, C-7A	3	5 1/4	800		6280		
	R-40	Med.	31069-8	■ X	400R40/FL	120	24	Swimming Pool	C, C-7A	3 3/4	6 3/4	2000				
			14431-1	■ ★ (31, 37, 51, 53)	400R40/FL	120	24	Swimming Pool	C, C-7A	3 3/4	6 3/4	2000		3500		
500	PAR-64	Ext. Mog. End Prong	23417-9	(9, 55)	500PAR64/MFL	120	6	PAR Med. Flood	C, CC-13			6	2000			
			23416-1		500PAR64/NSP	120	8	PAR Narrow Spot	C, CC-13			6	2000			
	PS-35	Mog.	37446-2	X (9, 46, 55)	500	120-130	24	Clear	C, C-9	7	9 3/4	1000				
			14407-1		500	120-130	24	Clear	C, C-9	7	9 3/4	1000		8900		
													2830	6755		
			14313-1		500/IF	120-130	24	Frost	C, C-9			9 3/4	1000		8700	
													2830	6600		
			37448-8	X	500/99	120-130	24	Clear Extended Service	C, C-9	7	9 3/4	2500		8750		
			14319-8		500/99	120-130	24	Clear Extended Service	C, C-9	7	9 3/4	2500		8100		
													7134	6145		
	PS-40	Mog.	14318-0		500/99IF	120-130	24	Frost Extended Service	C, C-9			9 3/4	2500		8000	
													7134	6080		
			14327-1		500		277	24	Clear	C, C-9			9 3/4	1000		7000
			14322-2		500PS40	120-130	24	Clear	C, C-9			9 3/4	1000		8300	
													2830	6300		
			23975-6	X (14, 31)	500/SBIF	120	24	Frost Silvered Bowl	C, C-9			9 3/4	1000		9500	
			14325-5		500/SBIF	120-130	24	Frost Silvered Bowl	C, C-9			9 3/4	1000		8300	
													2830	6300		
			14326-3		500/RS	120-130	24	Clear Rough Service	C, C-9			9 3/4	1000		8300	
													2830	6300		
R-40	Med.	33730-3	■ ★ X (31, 37, 51, 53, 12)	500R/3FL/2S	130	24	Swimming Pool	C, C-7A			6 3/4	2000		6120		
											5707	4669				
											5707	4669				
	Mog.	14430-3	■ ★ X (31, 37, 51, 53, 12)	500R/3FL/2S	130	24	Swimming Pool	C, C-7A			6 3/4	2000		6120		
												5707	4669			
		14434-5	★ (51, 53)	500R/3FL	120-130	24	Frost Reflector Flood	CC-11			7 3/4	2000		5000		
24783-3		★ X (51, 53)	500R/3FL	250	24	Frost Reflector Flood Special Service	C, C-7A			7 3/4	2000					
620	PS-40	Mog. Pf.	14323-0		620PS40P	120	24	Code Beacon	C, C-7A	5 1/4	10 3/4	3000		9000		

For the most current product information, go to the e-catalog on www.philips.com
Incandescent symbols and footnotes located on page 44