



PAR30 LED with AirFlux Technology

13PAR30L/END/4000/F25 DIM 6/1

Philips PAR30 Dimmable LED Lamps with AirFlux Technology provide optimal thermal efficiency in a sleek, lightweight design.

Product data

• General Characteristics

Cap-Base	E26
Bulb	PAR30L
Rated Avg. Life (Hours)	45000 hr
Rated Lifetime (years)	41.1 an

• Light Technical Characteristics

Color Code	CW
Color Designation	Cool White
Beam Angle	25 D
Beam Description	25D [Medium beam]
Correlated Color Temperature	4000 K
Approx. MBCP	3072 cd
CRI	80
Color Temp. (Kelvin)	4000 K [CCT 4000K]
Rated Luminous Flux	720 Lm

• Electrical Characteristics

Wattage	13 W
Wattage Technical	13 W
Voltage	120 V
Power Factor	0.72 -

Lamp Current mA	152 mA
Dimmable	Yes
Wattage Equivalent	75 W

• Measuring Conditions

Switching cycle	20000x
-----------------	--------

• Product Dimensions

Overall Length C	111.79 mm
Overall Length C [inch]	4.401 (max) in
Diameter D	92 mm

• Product Data

Product number	425330
Full product name	13PAR30L/END/4000/F25 DIM 6/1
Short product name	13PAR30L/END/4000/F25 DIM 6/1
Pieces per Sku	1
eop_pck_cfg	6
Skus/Case	6
Bar code on pack	46677425333
Bar code on case	50046677425338
Logistics code(s)	929000230004
eop_net_weight_pp	0.240 kg



PHILIPS

sense and simplicity