

Halogen Lamps

Mini Reflector, ALR, ALUline PRO III, Twistline and Linear Lamps

Watts	Bulb	Base	Product Number	Symbols, Footnotes	Ordering Code	Volts	Pkg. Qty.‡	Description	Class Filament	MOL (In.)	Rated Avg. Life (Hrs.)(93)	Approx. MBCP [†]	Lumens	Life Years (446)	Energy Cost (445)	Color Temp. (K)
-------	------	------	----------------	--------------------	---------------	-------	------------	-------------	----------------	-----------	----------------------------	---------------------------	--------	------------------	-------------------	-----------------

Halogen MR Aluminum (Formerly Continuum Pro) (92)

FTC REQUIREMENTS*

50	MRC16	GU5.3	13982-4		50 MRC16/FL36/A	12	50	Flood 36°	C, C-8	1½	5000	2100	950	4.6	\$6.02	3100
----	-------	-------	---------	--	-----------------	----	----	-----------	--------	----	------	------	-----	-----	--------	------

Closed Aluminum Reflector (ALR) Lamps Aluminum Reflector With Lens (92)

20	37mm	BA15d	32840-1		20ALR12/NSP6 GBD Clear	12	50	Clear, Narrow Spot 6°	C, C-8	1½	2000	7000	250	1.8	\$2.41	3000
			34002-6		20ALR12/SP18 GBE Frost	12	50	Frost, Spot 18°	C, C-8	1½	2000	1500	250	1.8	\$2.41	3000
			34003-4		20ALR12/FL32 GBF Frost	12	50	Frost, Flood 32°	C, C-8	1½	2000	750	250	1.8	\$2.41	3000
50	56mm	B15d	34091-9		50ALR18/NFL25 GBK Frost	12	50	Frost, Narrow Flood 25°	C, C-8	2¼	2000	2500	820	1.8	\$6.02	3000

ALUline PRO III

50	ALU	G53	Pro III	13396-6		ALU111MM 50W G53 12V 8D	12	6	Spot 8°	C, C-8	2¾	3000	23,000	950	2.7	\$6.02	3000
				13397-4		ALU111MM 50W G53 12V 24D	12	6	Flood 24°	C, C-8	2¾	3000	4000	950	2.7	\$6.02	3000
75	ALU	G53	Pro III	13398-2		ALU111MM 75W G53 12V 8D	12	6	Spot 8°	C, C-8	2¾	3000	30,000	1575	2.7	\$9.03	3000

Twistline GU10 Blister-Carded (98)

25	Twistline	GU10	41693-3	†	BC25TWISTLINE GU10/FL25	120	6	Blister Card, Flood 25°	C, C-6	2	2000	345	160	1.8	\$3.01	2700
35	Twistline	GU10	41573-7	†	BC35TWISTLINE GU10/FL25	120	6	Blister Card, Flood 25°	C, C-6	2	2000	480	265	1.8	\$4.22	2750
			41825-1	†	BC35GU10/HES/FL	120	6	Blister Card, Flood 25°	C, C-6	2	1500	800	410	1.4	\$4.22	3000
50	Twistline	GU10	41579-4	†	BC50GU10/HAL/TL	120	6	Blister Card, Flood 25°	C, C-6	2	2000	700	430	1.8	\$6.02	2800
			41574-5	†	BC50TWISTLINE GU10/FL25	120	6	Blister Card, Flood 25°	C, C-6	2	2000	700	430	1.8	\$6.02	2800

Halogen Single-Ended Linear Lamps Blister-Carded (95)

50	T4	Mini-Can	41555-4	†	BC50Q/CL	120	12	Blister Card	C, CC-8	2¾	1000	—	500	0.9	\$6.02	2700
75	T4	Mini-Can	41556-2	†	BC75Q/CL	120	12	Blister Card	C, CC-8	3	1000	—	1050	0.9	\$9.03	2700
			41886-3	†	BC75T4Q/HES/MC	120	12	Blister Card	C, CC-8	2¾	1500	—	1500	1.4	\$9.03	3000
100	T4	Mini-Can	41633-9	†	BC100Q/CL ESN	120	12	Blister Card	C, CC-8	2¾	1000	—	1600	0.9	\$12.05	2700
150	T4	Mini-Can	41634-7	†	BC150Q/CL ETG	120	12	Blister Card	C, CC-8	3	1000	—	2800	0.9	\$18.07	2700

For the most current product information, go to the e-catalog on www.philips.com
Halogen symbols and footnotes located on page 109

