

EL Style Malleable Elbows

Catalog Number: PREL296
UPC: 784011208074

Description

3/4 Inch M/F 90 Degree Malleable Elbow

PVC coated EL style malleable elbows with male and female threads (Male/Female) are used in a conduit run to change direction 90° or to terminate at a fitting or box.

Application

- Used in a conduit run to change direction 90 degree or to terminate at a fitting or box
- Used in a conduit run to change direction 90 degree or to terminate at a fitting or box

Features

- 40 mil gray PVC exterior coating
- 2 mil red urethane interior coating
- Various configurations in 10 trade sizes from 1/2" through 4"
- Sealing sleeves on all conduit openings

General

Material:	FERROUS METAL
Exterior Finish:	A nominal .040 inch (40 mil) gray PVC coating
Interior Finish:	A nominal .002 inch (2 mil) red urethane

Dimensions

Dimension A (Inches)	1.63
Nominal Weight (Pounds)	0.5

Technical / Specification Documents

Specification Guide (1995 Master)	AVAILABLE ON WEBSITE
Specification Guide (2004 Master)	AVAILABLE ON WEBSITE
Installer Certification and Tools	AVAILABLE ON WEBSITE
Chemical Resistance Charts	AVAILABLE ON WEBSITE
Performance Specifications	AVAILABLE ON WEBSITE

Standards

NEC/CEC:	Class I, Division 1 & 2, Groups A,B, C, D
NEC/CEC:	Class II, Division 1, Groups E, F, G
NEC/CEC:	Class II, Division 2, Groups F, G
NEC/CEC:	Class III

