

GUA Style Conduit Outlet Boxes

Catalog Number: PRGUAB47
 UPC: 784011205790

Description

1-1/4 Inch GUAB Outlet Box w/ Alum Cover (3-5/8" Open)

PVC coated GUA series conduit outlet boxes are installed in hazardous location conduit systems to serve as pull and splice boxes, to change the direction of a conduit run, to connect runs of conduit, or to provide access to conductors. Electrical continuity of the conduit system is maintained across assembled joints.

Application

- Installed in hazardous location to serve as pull and splice boxes, to change the direction of a conduit run, to connect runs of conduit, or to provide access to conductors

Features



- 40 mil gray PVC exterior coating
- 2 mil red urethane interior coating
- Trade sizes from 1/2" through 2" in various styles and configurations
- Sealing sleeves on all conduit openings
- Neoprene O-ring is standard
- Molded-in PVC seal preserves venting characteristics of fitting but seals out corrosives
- Standard material is a cast iron alloy body with a copper-free aluminum cover. Consult Factory for availability of cast iron covers
- Internal green grounding screw is standard

General


| | |
|------------------|---|
| Body Material: | FERROUS METAL |
| Cover Material: | Aluminum |
| Exterior Finish: | A nominal .040 inch (40 mil) gray PVC coating |
| Interior Finish: | A nominal .002 inch (2 mil) red urethane |
| Cover Seal: | Standard neoprene O-ring |
| PVC Seal: | Molded-in PVC seal preserves venting characteristics but seals out corrosives |
| Grounding: | Internal green grounding screw |

Dimensions

| | |
|-------------------------|-------|
| Cover Opening (Inches) | 3-5/8 |
| Dimension A (Inches) | 4.33 |
| Dimension B (Inches) | 2.73 |
| Dimension C (Inches) | 2.75 |
| Dimension D (Inches) | 1.13 |
| Nominal Weight (Pounds) | 5 |



An integral PVC gasket on GUA type fittings preserves the venting characteristics of the uncoated fitting but prevents corrosive liquids from entering from the outside.





GUA Style Conduit Outlet Boxes

Catalog Number: PRGUAB47
UPC: 784011205790

Technical / Specification Documents

| | |
|-----------------------------------|----------------------|
| Specification Guide (1995 Master) | AVAILABLE ON WEBSITE |
| Specification Guide (2004 Master) | AVAILABLE ON WEBSITE |
| Installer Certification and Tools | AVAILABLE ON WEBSITE |
| Chemical Resistance Charts | AVAILABLE ON WEBSITE |
| Performance Specifications | AVAILABLE ON WEBSITE |

Standards

| | |
|----------------|--------------------------------------|
| UL 514A, 514D: | E231035 |
| CSA: | C22.2 No. 18, C22.2 No. 42 |
| NEC/CEC: | Class I, Division 1 & 2, Groups C, D |
| NEC/CEC: | Class II, Division 1, Groups E, F, G |
| NEC/CEC: | Class II, Division 2, Groups F, G |
| NEC/CEC: | Class III |
| ANSI Standard: | C-33.27 |
| NEMA/EEMAC: | Type 3, Type 4 |