

F7 F8 M9 Conduit Bodies

Catalog Number: PRL87
UPC: 784011203888

Description

3 Inch Form 7 LL Conduit Body

PVC coated Form 7 conduit bodies with covers are offered in numerous configurations to provide a complete coated conduit system. Electrical continuity of the conduit system is maintained across assembled joints.

Application

- Offered in numerous configurations for 90 degree bends, taps or splices or mounting outlets
- Offered in numerous configurations for 90 degree bends, taps or splices or mounting outlets

Features

- 40 mil gray PVC exterior coating
- 2 mil red urethane interior coating
- 10 trade sizes from 1/2" through 4"
- Sealing sleeves on all conduit openings
- Cover uses retained stainless screw and wedge clip design

General



| | |
|------------------|---|
| Material: | FERROUS METAL |
| Exterior Finish: | A nominal .040 inch (40 mil) gray PVC coating |
| Interior Finish: | A nominal .002 inch (2 mil) red urethane |
| Body Style: | LL |
| Screw Type: | Self-retaining stainless steel cover screws |

Dimensions

| | |
|-------------------------|-------|
| Dimension A (Inches) | 10.54 |
| Dimension B (Inches) | 4.42 |
| Dimension C (Inches) | 5.79 |
| Dimension D (Inches) | 3.56 |
| Dimension E (Inches) | 8.38 |
| Nominal Weight (Pounds) | 12.7 |

Technical / Specification Documents

| | |
|-----------------------------------|----------------------|
| Specification Guide (1995 Master) | AVAILABLE ON WEBSITE |
| Specification Guide (2004 Master) | AVAILABLE ON WEBSITE |
| Installer Certification and Tools | AVAILABLE ON WEBSITE |
| Chemical Resistance Charts | AVAILABLE ON WEBSITE |
| Performance Specifications | AVAILABLE ON WEBSITE |





F7 F8 M9 Conduit Bodies

Catalog Number: PRL87
UPC: 784011203888

Standards

| | |
|----------------|--------------|
| UL 514A, 514D: | E231035 |
| CSA Certified: | C22.2 No.18 |
| CSA Certified: | C22.2 No. 42 |

Notes

Not available with encapsulated screws.
All cover screws are stainless steel

