

PVC Coated Nipples

Catalog Number: PRHNIP-2X6
UPC: 784011210541

Description

2X6 PVC Coated Nipple

Factory-threaded PVC coated nipples save time and money in the field. Electrical continuity is maintained across assembled joints.

Application

- Factory-threaded PVC coated nipples save time and money in the field

Features

- 40 mil gray PVC exterior coating
- 2 mil red urethane interior coating
- 12 trade sizes from 1/2" through 6"
- 11 standard lengths in available: Close, 2" to 12"
- Made to order lengths available - Call for quote
- Color-coded thread protector caps for quick identification of conduit size

General

Material:	STEEL
Exterior Finish:	A nominal .040 inch (40 mil) Gray PVC Coating
Interior Finish:	A nominal .002 inch (2 mil) red urethane
Thread Finish: Steel	A clear urethane coating over Hot Galvanized
Thread Protector Color:	Blue

Dimensions

Metric Size Designators	53
Pipe Size (Inches)	2
Outside Wall Thickness (Inches)	0.146
Diameter With Coating (Inches)	2.455
Internal Inside Diameter (Inches)	2.083
Length (Inches)	6

Technical / Specification Documents

Specification Guide (1995 Master)	AVAILABLE ON WEBSITE
Specification Guide (2004 Master)	AVAILABLE ON WEBSITE
Installer Certification and Tools	AVAILABLE ON WEBSITE
Chemical Resistance Charts	AVAILABLE ON WEBSITE
Performance Specifications	AVAILABLE ON WEBSITE





PVC Coated Nipples

Catalog Number: PRHNIP-2X6
UPC: 784011210541

Standards

UL 6:	E2314
CSA CERTIFIED:	C22.2 No. 45

Notes

The exteriors of certain short nipples are coated with urethane in lieu of PVC, dictated by the manufacturing process as well as assembly considerations.
