

## PVC Coated Nipples

Catalog Number: PRHNIP-3X12  
UPC: 784011210732

### Description

#### 3X12 PVC Coated Nipple

Factory-threaded PVC coated nipples save time and money in the field. Electrical continuity is maintained across assembled joints.

### Application

- Factory-threaded PVC coated nipples save time and money in the field

### Features

- 40 mil gray PVC exterior coating
- 2 mil red urethane interior coating
- 12 trade sizes from 1/2" through 6"
- 11 standard lengths in available: Close, 2" to 12"
- Made to order lengths available - Call for quote
- Color-coded thread protector caps for quick identification of conduit size

### General

Material:	STEEL
Exterior Finish:	A nominal .040 inch (40 mil) Gray PVC Coating
Interior Finish:	A nominal .002 inch (2 mil) red urethane
Thread Finish: Steel	A clear urethane coating over Hot Galvanized
Thread Protector Color:	Blue

### Dimensions

Metric Size Designators	78
Pipe Size (Inches)	3
Outside Wall Thickness (Inches)	0.205
Diameter With Coating (Inches)	3.58
Internal Inside Diameter (Inches)	3.09
Length (Inches)	12

### Technical / Specification Documents

Specification Guide (1995 Master)	AVAILABLE ON WEBSITE
Specification Guide (2004 Master)	AVAILABLE ON WEBSITE
Installer Certification and Tools	AVAILABLE ON WEBSITE
Chemical Resistance Charts	AVAILABLE ON WEBSITE
Performance Specifications	AVAILABLE ON WEBSITE





## PVC Coated Nipples

**Catalog Number:** PRHNIP-3X12

**UPC:** 784011210732

### Standards

---

UL 6: E2314

CSA CERTIFIED: C22.2 No. 45

---

### Notes

---

The exteriors of certain short nipples are coated with urethane in lieu of PVC, dictated by the manufacturing process as well as assembly considerations.

---