

Plasti-Bond REDH₂OT[®]

PLASTI-BOND REDH₂OT PRICE LIST • HUBS AND UNIONS

Knockout Hubs and Conduit Unions Cost and Shipping Information

PLASTI-BOND REDH₂OT KNOCKOUT HUBS

CATALOG NUMBER	DESCRIPTION	LIST PRICE	PER PRICING UNIT	WEIGHT PER PRICING UNIT	STANDARD PACK QTY	UPC	AVAIL. CODE
PRST1	1/2 KNOCKOUT HUB	21.84	EA	0.2	40	784011207367	1
PRST2	3/4 KNOCKOUT HUB	24.80	EA	0.3	25	784011207374	1
PRST3	1 KNOCKOUT HUB	31.01	EA	0.4	15	784011207381	1
PRST4	1-1/4 KNOCKOUT HUB	35.64	EA	0.4	15	784011207398	1
PRST5	1-1/2 KNOCKOUT HUB	40.75	EA	0.6	10	784011207404	1
PRST6	2 KNOCKOUT HUB	58.64	EA	1.2	5	784011207411	1
PRST7	2-1/2 KNOCKOUT HUB	91.75	EA	1.5	2	784011207428	1
PRST8	3 KNOCKOUT HUB	125.98	EA	2.1	2	784011207435	1
PRST9	3-1/2 KNOCKOUT HUB	163.44	EA	3.0	3	784011207442	3
PRST10	4 KNOCKOUT HUB	199.84	EA	3.5	1	784011207459	1
PRST11	5 KNOCKOUT HUB	239.83	EA	5.4	1	784011207466	3
PRST12	6 KNOCKOUT HUB	284.85	EA	6.9	1	784011207473	3
PRSTG1	1/2 KNOCKOUT HUB W/GRND	30.58	EA	0.2	40	784011207480	1
PRSTG2	3/4 KNOCKOUT HUB W/GRND	31.88	EA	0.3	25	784011207497	1
PRSTG3	1 KNOCKOUT HUB W/GRND	34.08	EA	0.4	15	784011207503	1
PRSTG4	1-1/4 KNOCKOUT HUB W/GRND	37.55	EA	0.4	15	784011207510	1
PRSTG5	1-1/2 KNOCKOUT HUB W/GRND	53.43	EA	0.6	10	784011207527	1
PRSTG6	2 KNOCKOUT HUB W/GRND	66.97	EA	1.2	4	784011207534	1
PRSTG7	2-1/2 KNOCKOUT HUB W/GRND	99.15	EA	1.5	5	784011207541	1
PRSTG8	3 KNOCKOUT HUB W/GRND	128.60	EA	2.1	4	784011207558	1
PRSTG9	3-1/2 KNOCKOUT HUB W/GRND	168.76	EA	3.0	2	784011207565	3
PRSTG10	4 KNOCKOUT HUB W/GRND	210.73	EA	3.5	3	784011207572	1
PRSTG11	5 KNOCKOUT HUB W/GRND	273.89	EA	5.4	1	784011207589	3
PRSTG12	6 KNOCKOUT HUB W/GRND	369.56	EA	6.9	1	784011207596	3

(OTHER STYLES OF KNOCKOUT HUBS AVAILABLE - CONSULT FACTORY FOR PRICE AND AVAILABILITY)

PLASTI-BOND REDH₂OT CONDUIT UNIONS – FERROUS

CATALOG NUMBER	DESCRIPTION	LIST PRICE	PER PRICING UNIT	WEIGHT PER PRICING UNIT	STANDARD PACK QTY	UPC	AVAIL. CODE
PRUNF105	1/2 FEMALE TO FEMALE UNION	30.00	EA	0.3	20	784011207701	1
PRUNF205	3/4 FEMALE TO FEMALE UNION	30.55	EA	0.5	12	784011207718	1
PRUNF215	3/4 - 1/2 FEMALE TO FEMALE UNION	30.55	EA	0.6	12	784011207725	2
PRUNF305	1 FEMALE TO FEMALE UNION	40.96	EA	0.7	12	784011207732	1
PRUNF405	1-1/4 FEMALE TO FEMALE UNION	65.95	EA	1.5	4	784011207749	2
PRUNF505	1-1/2 FEMALE TO FEMALE UNION	79.60	EA	2.3	4	784011207756	2
PRUNF605	2 FEMALE TO FEMALE UNION	106.04	EA	3.6	2	784011207763	2
PRUNF705	2-1/2 FEMALE TO FEMALE UNION	160.40	EA	5.0	4	784011207770	3
PRUNF805	3 FEMALE TO FEMALE UNION	221.14	EA	6.5	2	784011207787	2
PRUNF905	3-1/2 FEMALE TO FEMALE UNION	274.34	EA	8.2	4	784011207794	3
PRUNF1005	4 FEMALE TO FEMALE UNION	352.21	EA	10.0	2	784011207800	2
PRUNF012	5 FEMALE TO FEMALE UNION	***	EA	12.5	2	784011207817	3
PRUNF014	6 FEMALE TO FEMALE UNION	***	EA	14.8	2	784011207824	3
PRUNY105	1/2 FEMALE TO MALE UNION	31.05	EA	0.4	20	784011207831	1
PRUNY205	3/4 FEMALE TO MALE UNION	34.44	EA	0.7	12	784011207848	1
PRUNY215	3/4 - 1/2 FEMALE TO MALE UNION	36.47	EA	0.7	15	784011207855	2
PRUNY305	1 FEMALE TO MALE UNION	43.01	EA	1.3	12	784011207862	1
PRUNY405	1-1/4 FEMALE TO MALE UNION	69.71	EA	2.6	4	784011207879	2

*** Consult factory

(continued on next page...)