

## F7 F8 M9 Conduit Bodies

Catalog Number: PRC77  
UPC: 784011203512

### Description

#### 2-1/2 Inch Form 7 C Conduit Body

PVC coated Form 7 conduit bodies with covers are offered in numerous configurations to provide a complete coated conduit system. Electrical continuity of the conduit system is maintained across assembled joints.

### Application

- Offered in numerous configurations for 90 degree bends, taps or splices or mounting outlets
- Offered in numerous configurations for 90 degree bends, taps or splices or mounting outlets

### Features

- 40 mil gray PVC exterior coating
- 2 mil red urethane interior coating
- 10 trade sizes from 1/2" through 4"
- Sealing sleeves on all conduit openings
- Cover uses retained stainless screw and wedge clip design

### General

|                  |   |
|------------------|---|
| Material:        | FERROUS METAL                                 |
| Exterior Finish: | A nominal .040 inch (40 mil) gray PVC coating |
| Interior Finish: | A nominal .002 inch (2 mil) red urethane      |
| Body Style:      | Dimension C (Inches)                          |
| Screw Type:      | Self-retaining stainless steel cover screws   |

### Dimensions

|                         |      |
|-------------------------|------|
| Dimension A (Inches)    | 12   |
| Dimension B (Inches)    | 3.67 |
| Dimension C (Inches)    | 4.33 |
| Dimension D (Inches)    | 3.56 |
| Dimension E (Inches)    | 8.38 |
| Nominal Weight (Pounds) | 10   |

### Technical / Specification Documents

|                                   |                      |
|-----------------------------------|----------------------|
| Specification Guide (1995 Master) | AVAILABLE ON WEBSITE |
| Specification Guide (2004 Master) | AVAILABLE ON WEBSITE |
| Installer Certification and Tools | AVAILABLE ON WEBSITE |
| Chemical Resistance Charts        | AVAILABLE ON WEBSITE |
| Performance Specifications        | AVAILABLE ON WEBSITE |





## F7 F8 M9 Conduit Bodies

Catalog Number: PRC77

UPC: 784011203512

### Standards

---

UL 514A, 514D: E231035

---

CSA Certified: C22.2 No.18

---

CSA Certified: C22.2 No. 42

---

### Notes

---

Not available with encapsulated screws.

---

All cover screws are stainless steel

---

