



480Δ - 208Y/120  
480Δ Primary Volts - 208Y/120 Secondary Volts - 3Ø  
Dry Type Distribution Transformer - Three Phase

1017



Catalog #: T3045K0013B

**PRODUCT FEATURES**

- UL listed, CSA certified
- Meet DOE 2016 efficiency requirements
- UL Type 3R with Weather Shield
- Floor Mounted
- Ground Studs for use with non-metallic conduit
- Aluminum Bus termination
- Covered under Acme's 10 year limited warranty

**BENEFITS**

Quiet operation with sound levels below NEMA standards

**DOE**

Meets or exceed U.S. DOE 10 CFR Part 431

**UL STANDARD**

UL 1561

**CSA STANDARD**

C22.2 No. 47

**WARRANTY**

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

**GENERAL PRODUCT INFORMATION**

kVA:	45.00
Primary Voltage:	480Δ
Secondary Voltage:	208Y/120
Frequency:	60 Hz
ANFC Taps:	2
BNFC Taps:	4
Taps % Steps:	2.5%
Max Temperature Rise:	150°C
UL Insulation Class:	220°C

**PRODUCT MEASUREMENTS**

Height (In./cm):	25.50 (64.8)
Width (In./cm):	24.39 (61.9)
Depth (In./cm):	19.37 (49.2)

**CONFIGURATION**

Construction Type: Ventilated

Mounting Type: Floor  
Wiring Diagram: 22

**PACKAGING**

Ship Weight (Lbs/Kg): 441 (200.0)

**COMPLIANCES**

DOE: Meets or exceed U.S. DOE 10 CFR Part 431  
UL Standard: UL 1561  
UL Listed: File E12547  
CSA Standard: C22.2 No. 47  
CSA Listed: LR7357-32  
Warranty: Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)