



120 X 240 - 24
120 X 240 Primary Volts - 24 Secondary Volts - 1Ø
Industrial Control Transformer - Encapsulated

1053



Catalog #: AE010100

PRODUCT FEATURES

- UL and cUL listed
- Constructed out of electrical lamination with precision wound coils
- Fully encapsulated core and coil
- Available Fuse Kits and Accessories
- Covered under Acme's 10 year limited warranty

BENEFITS

- Molded terminal blocks with isolation barriers
- Dual labeling for easy product identification
- Heavy gauge steel mounting feet
- Fast wire connection terminal

UL STANDARD

UL 506

CSA STANDARD

C22.2 No 66

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

VA:	100
Primary Voltage:	120 X 240
Secondary Voltage:	24
Frequency:	50/60 Hz
Max Temperature Rise:	55°C
UL Insulation Class:	105°C

PRODUCT MEASUREMENTS

Height (In./cm):	3.09 (7.8)
Width (In./cm):	3.41 (8.6)
Depth (In./cm):	3.28 (8.3)

CONFIGURATION

Mounting Type:	Floor
Wiring Diagram:	AE01

PACKAGING

Ship Weight (Lbs/Kg):	4.05 (1.8)
-----------------------	------------

COMPLIANCES

UL Standard: UL 506
UL Listed: File E79947
CSA Standard: C22.2 No 66
CSA Listed: LR7357-16
Warranty: Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf